



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED7T824GC835D 7W Led T8 24" 35K Line Volt

Keystone Technologies

Catalog Number	LED7T824GC835D
Manufacturer	Keystone Technologies
Description	7W Led T8 Tube, Shatter-Proof Coated Glass, 120-277V Input, 2, 3500K, Direct Drive
Weight per unit	0.3000 (lbs/each)
Product Category	Shape & Circular Lamps

Features

Ballast Type	N/A
beam angle	240 Deg
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	1000
Nominal Length	24 in
Nominal Size	N/A
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	7
Wire Type	N/A

Material, Color, and Finish

Base Type	G13
color rendering index (cri)	>80 Deg
color temperature	3500
housing color	N/A

Descriptions

Construction	Frosted Shatterproof Glass
Description	7W LED T8 24" 35K LINE VOLT
extra long description	Key KT-LED7T8-24GC-835-D-CP 7W, 100
Long Description	7W LED T8 TUBE, SHATTER-PROOF COATED GLASS, 120-277V INPUT, 2, 3500K, DIRECT DRIVE
Product Type	7W, 1000 Lumen, 2', 240' Beam Angle, Ballast Bypass, DLC 4.0

Manufacturer Information

Brand	Keystone
GTIN	00890949013199
Manufacturers Part Number	KT-LED7T8-24GC-835-D-CP
UPC	890949013199



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
----------------------	--

Packaging

Carton	25
--------	----

Weight Per each	0.3
-----------------	-----

Uses, Certifications, and Standards

Energy Star	N
-------------	---