



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED8029E40A 24W Led BLRD/PST Top 42K Edsn Base *Light Efficient Design*

Catalog Number	LED8029E40A
Manufacturer	Light Efficient Design
Description	Speciality Led Lamp, 360 ° Beam Angle, 82, 4000 K, 3422 LM Brightness (Lumens), 24 W, 120 to 277 V, 50000 H Average Life, E26 Edison Base, Non Dimmable, 2.9 In Diameter, 6.75 In Length, 0.983 Power Factor, -40 °F Operating Temperature, +122 °F Operating Temperature, 100 W, 5 Yr Warranty, 0.72 LB
Weight per unit	0.7200 (lbs/each)
Product Category	Led Specialty Lamps & Modules

Features

Base	E26
dimnable	No
lumens	3422.4

Material, Color, and Finish

color rendering index (cri)	82
-----------------------------	----

Descriptions

Description	24W LED BLRD/PST TOP 42K EDSN BASE
extra long description	LED LED-8029E40-A 24W Mini Bollard

Manufacturer Information

GTIN	00844006080631
UPC	844006080631

Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
----------------------	-------------------------------

Packaging

Carton	1
Weight Per each	0.72

Uses, Certifications, and Standards

standard	cULus
----------	-------