



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED8038E40A *Delisted* 14W Led BLRD/PST Top 40K E26 Base *Light Efficient Design*

Catalog Number	LED8038E40A
Manufacturer	Light Efficient Design
Description	Speciality Led Lamp, 360 ° Beam Angle, 82.1, 4000 K, 2065 LM Brightness (Lumens), 14 W, 120 to 277 V, 50000 H Average Life, E26 Base, Non Dimmable, 2.6 In Diameter, 5.4 In Length, 0.973 Power Factor, -40 °F Operating Temperature, +122 °F Operating Temperature, 70 W, 5 Yr Warranty, 0.46 LB
Weight per unit	0.4600 (lbs/each)
Product Category	Led Specialty Lamps & Modules

Features

Base	E26
dimnable	No
lumens	2217.4

Material, Color, and Finish

color rendering index (cri)	81.5
-----------------------------	------

Descriptions

Description	*DELISTED* 14W LED BLRD/PST TOP 40K E26 BASE
extra long description	LED LED-8038E57-A 14W BOLLARD RETRO

Manufacturer Information

GTIN	00844006082970
Manufacturers Part Number	LED-8038E57-A
UPC	844006082970

Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
----------------------	-------------------------------

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Weight Per each	0.46

Uses, Certifications, and Standards

standard	cULus
----------	-------