



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED8039E57A 18W Led Hid RPLCMT 30K

Light Efficient Design

Catalog Number	LED8039E57A
Manufacturer	Light Efficient Design
Description	Speciality Led Lamp, 360 ° Beam Angle, 82.2, 3000 K, 2465 LM Brightness (Lumens), 18 W, 100 to 277 V, 50000 H Average Life, E26 Edison Base, Non Dimmable, 2.6 In Diameter, 6.1 In Length, 0.977 Power Factor, -40 °F Operating Temperature, +122 °F Operating Temperature, 5 Yr Warranty, 0.57 LB
Weight per unit	0.5700 (lbs/each)
Product Category	Led Specialty Lamps & Modules

Features

Base	E26
dimnable	No
lumens	3071

Material, Color, and Finish

color rendering index (cri)	82.2
-----------------------------	------

Descriptions

Description	18W LED HID RPLCMT 30K
extra long description	LED LED-8039E57-A 18W Mini Bollard

Manufacturer Information

GTIN	00844006080488
UPC	844006080488

Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
----------------------	-------------------------------

Packaging

Carton	1
Weight Per each	0.57

Uses, Certifications, and Standards

standard	cULus
----------	-------