

LED Dimmable Globe

25,000 Hours average rated life, 120Volts

Applications:


Ideal for dimmable A-lamp applications.

- + Vanity Strips
- + Pendant Lighting
- + Decorative



Features and Benefits

- Smooth, uniform dimming from 100% to 5%.
- Energy Efficient: Up to 80% less energy than standard incandescent.
- Exceeds all industry performance requirements for non-standard lamps.
- Long life: 25,000 hours (lasts at least 15 times longer than alternative)
- Very Durable: Solid state lighting technology significantly reduces lighting service & maintenance due to robust lighting design.
- Excellent Color consistency and high color rendering (CRI).



Specifications

Input Line Voltage:	120 VAC
Input Power	5W/8W
Input Line Frequency	50
Lamp Life (Rated)	25,000 hrs
Minimum Starting Temp	-20°C
Maximum Operating Temp	40°C

Warranties and Certifications:	Item #	Description	Voltage	Wattage	Wattage Equivalent	M.O.L. (inches)	Diameter (inches)	Lumens	LPW	Beam Angle	CCT	CRI
3 YEAR WARRANTY	LED5G25D27KF	Dimmable 5W Smooth G25 - 2700K, Frosted	120	5	40	4.3	3.1	300	60.0	230	2700K	82
	LED5G25D30KF	Dimmable 5W Smooth G25 - 3000K, Frosted	120	5	40	4.3	3.1	325	65.0	230	3000K	82
	LED8G25D27KF	Dimmable 8W Smooth G25 - 2700K, Frosted	120	8	60	4.3	3.1	500	62.5	230	2700K	82
	LED8G25D30KF	Dimmable 8W Smooth G25 - 3000K, Frosted	120	8	60	4.3	3.1	525	65.6	230	3000K	82
For the most up-to-date specs, please visit www.tcpi.com												