



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED9300 2X4 High Bay 38K Lumens *Light Efficient Design*

Catalog Number	LED9300
Manufacturer	Light Efficient Design
Description	High Bay Led Fixture, Commercial and Industrial Buildings Application, 50000 H Average Life, 120 ° Beam Angle, Wide Beam Spread, 38533 LM Brightness (Lumens), 83.9 Color Rendering Index, 5000 K Color Temperature, Not Dimmable, 1000 W (Hid) Equivalent Wattage, High Bay Led Fixture Fixture Type, 2.75 In;69.9 MM Height, Diffuser Lens;Hanging Cable Includes, Led Lamp Type, 1219 MM;48 In Length, Culus Listed;DLC Listed;Rohs Compliant, 120 to 277 V Voltage Rating, 5 Yr Warranty, 300 W Wattage, 30 LB Weight, 23.8
Weight per unit	30.0 (lbs/each)
Product Category	Led Highbay Lighting

Features

Base	Not Applicable
dimnable	No
lumens	38533
Power Factor	1000W HID

Material, Color, and Finish

color rendering index (cri)	83.9
-----------------------------	------

Dimensions and Weight

Diameter	23.8
----------	------

Descriptions

Description	2X4 HIGH BAY 38K LUMMENS
extra long description	LED LED-9300-50K 300W Replaces 1000

Manufacturer Information

Brand	Light Efficient Design
GTIN	00844006093006
Manufacturers Part Number	LED-9300-50K
UPC	844006093006

Taxonomies, Classifications, and Categories

Category Description	LED HIGHBAY, LOWBAY & INDUSTRIAL LIGHTING
----------------------	---

Packaging

Carton	1
Weight Per each	30

Uses, Certifications, and Standards

standard	cULus
----------	-------