



Product 78035

Number:

Order LED9A19DIMO827URP

Abbreviation:

General LED A19, 9W, Dimmable, 80CRI, 800 Lumen, 2700K, 15000 life

Description:

Product Information

Life Time (L70)	15000
Operating Temperature (°C)	-20 to 45
Dimming	Yes
Abbrev. With Packaging Info.	LED9A19DIMO827URP 6/CS 1/SKU
Average Rated Life (hr)	15000
Base	E26 Medium
Bulb	A19
Family Brand Name	ULTRA
Color Temperature/CCT (K)	2700
Color Rendering Index (CRI)	80
Lumens	800
Approx. Lumens	800
Nominal Voltage (V)	120.00
Nominal Wattage (W)	9.00
Language Strategy	ENGLISH/FRENCH
Ordering Abbreviation	LED9A19DIMO827URP
UPC Code	UPC046135780356
Lamp Finish	Frosted



Product 78035

Number:

Order LED9A19DIMO827URP

Abbreviation:

General LED A19, 9W, Dimmable, 80CRI, 800 Lumen, 2700K, 15000 life

Description:

Product Information

Life Time (L70)	15000
Operating Temperature (°C)	-20 to 45
Dimming	Yes
Abbrev. With Packaging Info.	LED9A19DIMO827URP 6/CS 1/SKU
Average Rated Life (hr)	15000
Base	E26 Medium
Bulb	A19
Family Brand Name	ULTRA
Color Temperature/CCT (K)	2700
Color Rendering Index (CRI)	80
Lumens	800
Approx. Lumens	800
Nominal Voltage (V)	120.00
Nominal Wattage (W)	9.00
Language Strategy	ENGLISH/FRENCH
Ordering Abbreviation	LED9A19DIMO827URP
UPC Code	UPC046135780356
Lamp Finish	Frosted