



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LED9A19DIM0840UR 9W Led A19 40K Dim 800LM *Sylvania-Ledvance*

Catalog Number	LED9A19DIM0840UR
Manufacturer	Sylvania-Ledvance
Description	Led A19, 9W, Dimmable, 80CRI, 800 Lumen, 4000K, 15000 Life, E26 Medium Base, Frosted Finish
Weight per unit	0.3100 (lbs/each)
Product Category	Lighting

Features

average life	15000
Base	E26 Medium
Lamp Type	LED A19
lumens	800
Shape	A19
Voltage	120.00 V
Voltage Rating	120.00
Wattage	9.00

Material, Color, and Finish

color rendering index (cri)	80
Style	A-shape

Dimensions and Weight

Size	2.36
------	------

Descriptions

Description	9W LED A19 40K DIM 800LM
extra long description	SYL LED9A19DIM0840URP/41190 LED9A19
Long Description	LED A19, 9W, Dimmable, 80CRI, 800 Lumen, 4000K, 15000 Life, E26 Medium Base, FROSTED Finish
Product Type	LED9A19DIM0840URP 6/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135411908
Manufacturers Part Number	LED9A19DIM0840URP/41190
UPC	046135411908

Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
----------------------	------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight Per each	0.31

Uses, Certifications, and Standards

standard	RoHS
----------	------