



LED-DK6-19W830-DIM



Description DISC LED GEN4 Downlight Kit 6 inch 19W - 1,200lm
Dimmable 2BD 80+CRI 120VAC E26 with GU24 Adapter

Ordering Code 08660

Specifications

| | |
|-------------------------------------|----------------------------------|
| Voltage Rating | 120 |
| Voltage Type | AC/DC |
| Watts | 19 |
| Base Type | Medium Screw (E26) |
| MOL in/mm | 3.84/97.5 |
| MOD in/mm | 7.28/185 |
| Lumens | 1200 |
| CT deg K | 3000 |
| CRI | 80 |
| Beam Angle | 120 |
| Rated Life | 35,000 |
| Ambient Operating Temp Range | -20° C (-4° F) to 40° C (104° F) |

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335



LED-DK6-19W830-DIM



Description DISC LED GEN4 Downlight Kit 6 inch 19W - 1,200lm
Dimmable 2BD 80+CRI 120VAC E26 with GU24 Adapter

Ordering Code 08660

| Specifications | |
|-------------------------------------|----------------------------------|
| Voltage Rating | 120 |
| Voltage Type | AC/DC |
| Watts | 19 |
| Base Type | Medium Screw (E26) |
| MOL in/mm | 3.84/97.5 |
| MOD in/mm | 7.28/185 |
| Lumens | 1200 |
| CT deg K | 3000 |
| CRI | 80 |
| Beam Angle | 120 |
| Rated Life | 35,000 |
| Ambient Operating Temp Range | -20° C (-4° F) to 40° C (104° F) |

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335