



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LEDRT56G900SC3 10W 27-50K CCT Selectable 90CRI 900LMN Gimbal *Sylvania-Ledvance*

Catalog Number	LEDRT56G900SC3
Manufacturer	Sylvania-Ledvance
Description	Led RT56 Gimbal, 10W, Dimmable, 90CRI, 900 Lumens, Selectable 2700, 3000, 3500, 4000, 5000K, 50000 Life
Weight per unit	0.9130 (lbs/each)
Product Category	Lighting

Features

Base	E26 Medium
Lamp Type	LED RT56 GIMBAL
Power Factor	> 0.90
Shape	SPECIAL
Voltage Rating	120
Wattage	10.00

Material, Color, and Finish

color rendering index (cri)	90
-----------------------------	----

Dimensions and Weight

Size	7.28
------	------

Descriptions

Description	10W 27-50K CCT SELECTABLE 90CRI 900LMN GIMBAL
extra long description	SYL LED/RT56G/900/SC3/65121 LEDRT56
Long Description	LED RT56 Gimbal, 10W, Dimmable, 90CRI, 900 Lumens, Selectable 2700, 3000, 3500, 4000, 5000K, 50000 life
Product Type	LEDRT56G900SC3 4/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135651212
Manufacturers Part Number	LED/RT56G/900/SC3/65121
UPC	046135651212

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
----------------------	--

Packaging

Carton	1
Weight Per each	0.913

Uses, Certifications, and Standards

standard	CEC
----------	-----