



## LENRK100 100A 250V Class RK1 Dual Element Time Delay Fuse

*Edison Fuses*

Catalog Number	LENRK100
Manufacturer	Edison Fuses
Description	Eaton Edison Lenrk Fuse, Non-Indicating, High In-Rush Current Motor Protection, Electrically Isolated End Caps, 100 A, Class RK1, 200 Kaic, Standard, 5, 250 V, 125 VDC
Weight per unit	0.0010 (lbs/each)
Product Category	Dual Element

### Features

amperage rating	100
Fuse Class	Class RK1
interrupt rating	200
media	Yes
Voltage Rating	250 VAC, 125 VDC

### Dimensions and Weight

Height	1.1
Length	5.88
Width	1.1

### Descriptions

Description	100A 250V CLASS RK1 DUEL ELEMENT TIME DELAY FUSE
extra long description	EFSE LENRK100 UL CLASS RK1 TIME DEL
Features	Edison offers a complete lineup of UL Class RK1 fuses with the LENRK and LSRK dual-element, time-delay fuses along with the NCLR and SCLR fast-acting fuses.
Long Description	Eaton Edison LENRK fuse, Non-indicating, High in-rush current motor protection, Electrically isolated end caps, 100 A, Class RK1, 200 kAIC, Standard, 5, 250 V, 125 Vdc
Product Type	UI Class RK1 Time Delay 2
Special Features	70/30 Brass End Cap

### Manufacturer Information

Brand	EDISON
GTIN	00782634538455
Manufacturers Part Number	LENRK100
UPC	782634538455

### Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	FUSE



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.001

## Uses, Certifications, and Standards

Application standard	Datacenters - Facilities: Critical Power CSA Certified,UL Listed,RoHS Compliant
----------------------	--