



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LENRK125 125A 250V Class RK1 Dual Element Time Delay Fuse

Edison Fuses

Catalog Number	LENRK125
Manufacturer	Edison Fuses
Description	Eaton Edison Lenrk Fuse, Non-Indicating, High In-Rush Current Motor Protection, Electrically Isolated End Caps, 125 A, Class RK1, 200 Kaic, Standard, 1, 250 V, 125 VDC
Weight per unit	0.0010 (lbs/each)
Product Category	Dual Element

Features

amperage rating	125 A
class	Class RK1
dimensions	7.1300 IN X 1.6100 IN X 1.6100 IN
interrupt rating	200 kAIC
media	Yes
Voltage Rating	250 VAC, 125 VDC

Descriptions

Description	125A 250V CLASS RK1 DUEL ELEMENT TIME DELAY FUSE
extra long description	EFSE LENRK125 UL CLASS RK1 TIME DEL
Features	Edison offers a complete lineup of UL Class RK1 fuses with the LENRK and LESRK dual-element, time-delay fuses along with the NCLR and SCLR fast-acting fuses.
Long Description	Eaton Edison LENRK fuse, Non-indicating, High in-rush current motor protection, Electrically isolated end caps, 125 A, Class RK1, 200 kAIC, Standard, 1, 250 V, 125 Vdc
Product Type	UI Class RK1 Time Delay 2
Special Features	Non-indicating, High in-rush current motor protection

Manufacturer Information

Brand	EDISON
GTIN	00782634538479
Manufacturers Part Number	LENRK125
UPC	782634538479

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	FUSE

Packaging

Carton	1
Weight Per each	0.001



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application
standard

Datacenters - Facilities: Critical Power

CSA Certified, UL Listed, RoHS Compliant