



LF430CWKN 30W Led FLD 50K KNKL MNT

Westgate MFG, Inc.

Catalog Number	LF430CWKN
Manufacturer	Westgate MFG, Inc.
Description	Housing Die-Cast Aluminum Housing With Powder Coat Finish (Dark Bronze) Voltage 120-277V, 60HZ Ac Tir Optic Lens - Type II Cord Type 13XAMPRESHX34, #18 Awg Stranded Wires Power Factor .9~.97 Operating Temp-40XAMPRESHX176, F to 104XAMPRESHX176, F Up to 110 Lumens Per Watt Cri 82~84 70, 000 Hour Rated Life, 7-Year Warranty Suitable For Wet Locations, Ip65
Weight per unit	3.1 (lbs/each)
Product Category	Lighting

Features

bulb type	LED
Category	Landscape Ltg.
Safety Rating	UL,DLC
Voltage	120.00 LBS

Material, Color, and Finish

Finish	Bronze/Dark
Style	Transitional

Descriptions

Description	30W LED FLD 50K KNKL MNT
Long Description	Housing Die-cast aluminum housing with powder coat finish (Dark Bronze) Voltage 120~277V, 60Hz AC TIR optic lens - TYPE II Cord Type 13xAMPRESHx34, #18 AWG stranded wires Power Factor .9~.97 Operating Temp-40xAMPRESHx176,F to 104xAMPRESHx176,F Up to 110 lumens per watt CRI 82~84 70,000 hour rated life, 7-year warranty Suitable for Wet Locations, IP65
Product Type	Led Flood Light

Manufacturer Information

Brand	Westgate MFG, Inc.
GTIN	00845060004045
Manufacturers Part Number	LF4-30CW-KN
UPC	845060004045

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	Spot/Flood



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Manufacturer Status Inactive

Packaging

Carton 1

Weight Per each 3.09