



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LHBS2436UNVL8405 155/246W Led High Bay 4K/5K 24000-36000LM

Cooper Lighting Solutions

Catalog Number	LHBS2436UNVL8405
Manufacturer	Cooper Lighting Solutions
Description	Linear Lensed High Bay Selectable, 24K and 36K Select, Diffused Lens, Universal Voltage 120-277, 4000K and 5000K CCT Select, 0-10V Dimming Driver, Unit Pack
Weight per unit	6.5 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.88A at 277V
Lamp Type	LED
Socket Type	N/A
Voltage Rating	120-277V

Material, Color, and Finish

Style	(blank)
-------	---------

Descriptions

Description	155/246W LED HIGH BAY 4K/5K 24000-36000LM
extra long description	CLS LHBS-2436-UNV-L84050-U LINEAR H
Long Description	Linear Lensed High Bay Selectable, 24K and 36K Select, Diffused Lens, Universal Voltage 120-277, 4000K and 5000K CCT select, 0-10V Dimming Driver, Unit Pack
Product Type	Linear HB, 24K36K LM, 120-277V, 4K/5K
Special Features	Superior performance: Up to 36,000 lumens and 160 lm/W

Manufacturer Information

Brand	METALUX
GTIN	00080083276141
Manufacturers Part Number	LHBS-2436-UNV-L84050-U
UPC	080083276141

Taxonomies, Classifications, and Categories

Category Description	LED HIGHBAY, LOWBAY & INDUSTRIAL LIGHTING
Type	INDUSTRIAL

Packaging

Carton	1
Weight Per each	6.5

Uses, Certifications, and Standards

Application	lighting
Mounting	Suspended
standard	UL Listed;DLC Certified;Title 24 Compliant;ISO Certified