



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LML01 3/8" Sealight 90DEG Conn

Appleton/Oz Gedney

Catalog Number	LML01
Manufacturer	Appleton/Oz Gedney
Description	Conduit Fittings, LML 90 Liquidtight Connectors, Material: Zinc Diecast, UL Standard: 514B, Trade Size: 3/8-1/2, Dimension: Height 2.40 Inches, Width 2.15 Inches, Thread Length .53
Weight per unit	0.2000 (lbs/each)
Product Category	Liquid Tight Fittings

Features

connection	Male NPS Thread
Connector Type	Compression
insulation	Non Insulated
Material	Zinc Die Cast

Material, Color, and Finish

Color	Metallic
Finish	Natural

Dimensions and Weight

Size	0.375
------	-------

Descriptions

Description	3/8" SEALTIGHT 90DEG CONN
extra long description	EGS LML-01 3/8 IN 90D CONN LFMC/LFN
Long Description	Conduit Fittings, LML 90 Liquidtight Connectors, Material: Zinc Diecast, UL Standard: 514B, Trade Size: 3/8-1/2, Dimension: Height 2.40 Inches, Width 2.15 Inches, Thread Length .53
Product Type	3/8 In 90D Conn LFMC/LFNC
Special Features	2.15 IN Length X 2.4 IN Height, 0.53 IN Thread Length, For Liquidtight Flexible Metal Conduit and Type B Non-Metallic Conduit, Liquidtight/Raintight/Oiltight

Manufacturer Information

Brand	Appleton
GTIN	00687855383016
Manufacturers Part Number	LML01
UPC	687855383016

Taxonomies, Classifications, and Categories

Category Description	METALLIC FITTINGS
Type	90 Deg Liquid Tight Conduit Connector

Trade Size

Trade Size	0.5
------------	-----



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Package	50
Weight Per each	0.2

Uses, Certifications, and Standards

Application	For Terminating Liquidtight Flexible Metal Conduit to a Enclosure at a 90 Degree Angle
environmental conditions	Rain Tight, Oil Tight, Liquid Tight
nema rating	FB-1
standard	CSA Certified: 208044;CSA Standard: C22.2 No. 18.3;NEMA: FB-1;UL Listed: E32539;UL Standard: 514B