



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LR150DCG 1-1/2" LR Condulet W/C&G *Appleton/Oz Gedney*

Catalog Number	LR150DCG
Manufacturer	Appleton/Oz Gedney
Description	Emt Conduit Bodies, Aluminum Threaded For Rigid Conduit and Imc, Series: LR, Material: Conduit Body: Diecast, Copperfree Aluminum/Epoxy Powder Coat, Cover: Stamped Aluminum, Natural Fi Nish, Gasket: Neoprene, Ul Standard: 514A, Trade Size: 1-1/2"
Weight per unit	1.0 (lbs/each)
Product Category	Alum

Features

Material	Die Cast Aluminum
----------	-------------------

Material, Color, and Finish

Finish	Epoxy Powder Coat
--------	-------------------

Dimensions and Weight

Height	2.97
Hub Size	2
Length	10.2
Width	3.83

Descriptions

Description	1-1/2" LR CONDULET W/C&G
extra long description	EGS LR150DCG 1-1/2 THD ALUM LR BDY
Long Description	EMT Conduit Bodies, Aluminum Threaded for rigid conduit and IMC, Series: LR, Material: Conduit body: diecast, copperfree aluminum/epoxy powder coat, Cover: stamped aluminum, natural fi nish, Gasket: neoprene, UL Standard: 514A, Trade Size: 1-1/2"
Product Type	1-1/2 THD Alum LR Bdy CVR GSKT
Special Features	1-1/2 IN Trade Size, Type LR Aluminum Threaded Conduit Body, Maximum No. of Conductors 3 - #1/0AWG, Volume 35.80 IN ³ , For Use With Rigid and IMC Conduit, Furnished With Stamped Aluminum Cover and Neoprene Gasket

Manufacturer Information

Brand	Appleton
GTIN	00687855000784
Manufacturers Part Number	LR150DCG
UPC	687855000784



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	FORM 5 CONDULETS, COVERS, & GASKETS
Type	Conduit Body

Packaging

Carton	10
Weight Per each	1

Uses, Certifications, and Standards

Application	Provides access to the interior of the raceway for wire pulling , splicing and maintenance, Allows connection of straight and branch conduit runs and 90 degree bends
standard	CSA Certified: 208044;CSA Standard: C22.2 No. 18.3;NEMA: FB-1;UL Listed: E53330;UL Standard: 514A