



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LT114200 1-1/4" Met L/T, Non UI 200' *Southwire Company*



Catalog Number	LT114200
Manufacturer	Southwire Company
Description	Liquidtight Flexible Conduit, 1-1/4 In Trade Size, 1.63 to 1.66 In Conduit Outer Diameter, 1.38 to 1.41 In Conduit Inner Diameter, Extra Flexible Style, 200 FT Length, Galvanized, Gray, 8 In Bend Radius, +14 °F Operating Temperature, +140 °F Operating Temperature, 73 LB/100 FT
Weight per unit	0.6000 (lbs/each)
Product Category	Liquid Tight Conduit

Features

outside diameter	1645
------------------	------

Descriptions

Description	1-1/4" MET L/T, NON UL 200'
extra long description	SWC 55107003 Titan2 Type EF Extra-F

Manufacturer Information

GTIN	00032886043079
UPC	032886043079

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
----------------------	--------------

Packaging

Carton	200
Weight Per each	0.6