



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LT1400 1" Met L/T, Non UI 400' *Southwire Company*



Catalog Number	LT1400
Manufacturer	Southwire Company
Description	Liquidtight Flexible Conduit, 1 In Trade Size, 1.29 to 1.315 In Conduit Outer Diameter, 1.041 to 1.066 In Conduit Inner Diameter, Titan(R) Ef Style, 400 FT Length, Galvanized, Gray, 6.5 In Bend Radius, +14 °F Operating Temperature, +140 °F Operating Temperature, 58 LB/100 FT
Weight per unit	0.4300 (lbs/each)
Product Category	Liquid Tight Conduit

Features

outside diameter	1302
------------------	------

Descriptions

Description	1" MET L/T, NON UL 400'
extra long description	SWC 55106803 Titan2 Type EF Extra-F

Manufacturer Information

GTIN	00032886043055
UPC	032886043055

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
----------------------	--------------

Packaging

Carton	400
Weight Per each	0.43