



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

LT2100 2" Met L/T, Non UI 100' *Southwire Company*



Catalog Number	LT2100
Manufacturer	Southwire Company
Description	Liquidtight Flexible Conduit, 2 In Trade Size, 2.34 to 2.375 In Conduit Outer Diameter, 2.02 to 2.045 In Conduit Inner Diameter, Titan(R) Ef Style, 100 FT Length, Galvanized, Gray, 12 In Bend Radius, +14 °F Operating Temperature, +140 °F Operating Temperature, 131 LB/100 FT
Weight per unit	1.1 (lbs/ft)
Product Category	Liquid Tight Conduit

Features

outside diameter	2277
------------------	------

Descriptions

Description	2" MET L/T, NON UL 100'
extra long description	SWC 55107203 Titan2 Type EF Extra-F

Manufacturer Information

GTIN	00032886043116
UPC	032886043116

Taxonomies, Classifications, and Categories

Category Description	Liquid Tight
----------------------	--------------

Availability

minimum qty	100
-------------	-----

Packaging

Carton	100
Weight Per foot	1.1