



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LU1000ECO 1000W E25 High Pressure Sodium Clear Mogul Base

Ge By Current Lamps

| | |
|------------------|--|
| Catalog Number | LU1000ECO |
| Manufacturer | Ge By Current Lamps |
| Description | High Pressure Sodium Lamp, 22, 2100 K, 140000 LM Brightness (Lumens), 1000 W, 456 V, Clear, Glass Material, 24000+ H Average Life, Mogul Base, S52 Ansi Ballast Code, Non Dimmable, 3.125 In Diameter, 15.06 In Length, 24.75 % Mercury Content, 0.96 LB |
| Weight per unit | 0.9600 (lbs/each) |
| Product Category | Hid High Pressure Sodium Lamps |

Features

| | |
|--------|--------|
| Base | E39 |
| lumens | 130000 |

Material, Color, and Finish

| | |
|-----------------------------|---------------------------|
| Color | Clear |
| color rendering index (cri) | 22.0 |
| Style | Open or enclosed fixtures |

Descriptions

| | |
|------------------------|---|
| Description | 1000W E25 HIGH PRESSURE SODIUM CLEAR MOGUL BASE |
| extra long description | GEL LU1000/ECO 44058 LUCALOX |
| Special Features | 15.06IN Length |

Manufacturer Information

| | |
|-------|----------------------|
| Brand | Ge Traditional Lamps |
| GTIN | 00043168440585 |
| UPC | 043168440585 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------|
| Category Description | SODIUM |
|----------------------|--------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 6 |
| Weight Per each | 0.96 |

Uses, Certifications, and Standards

| | |
|-------------|----------------------------|
| Application | Universal burning position |
|-------------|----------------------------|