



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LU1000ECO 1000W E25 High Pressure Sodium Clear Mogul Base

*Ge By Current Lamps*

Catalog Number	LU1000ECO
Manufacturer	Ge By Current Lamps
Description	High Pressure Sodium Lamp, 22, 2100 K, 140000 LM Brightness (Lumens), 1000 W, 456 V, Clear, Glass Material, 24000+ H Average Life, Mogul Base, S52 Ansi Ballast Code, Non Dimmable, 3.125 In Diameter, 15.06 In Length, 24.75 % Mercury Content, 0.96 LB
Weight per unit	0.9600 (lbs/each)
Product Category	Hid High Pressure Sodium Lamps

### Features

Base	E39
lumens	130000

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	22.0
Style	Open or enclosed fixtures

### Descriptions

Description	1000W E25 HIGH PRESSURE SODIUM CLEAR MOGUL BASE
extra long description	GEL LU1000/ECO 44058 LUCALOX
Special Features	15.06IN Length

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168440585
UPC	043168440585

### Taxonomies, Classifications, and Categories

Category Description	SODIUM
----------------------	--------

### Packaging

Carton	1
Package	6
Weight Per each	0.96

### Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------