



<b>Description</b>	400W HPS ED-18 Mogul Base
<b>Ordering Code</b>	15322
<b>UNSPSC Code</b>	39101617

## Specifications

<b>Voltage Rating</b>	100
<b>Watts</b>	400
<b>Base Type</b>	Mogul Screw (E39)
<b>Bulb Type</b>	ED-18
<b>MOL in/mm</b>	9.75/247.6
<b>MOD in/mm</b>	2.28/58.0
<b>LCL in/mm</b>	5.75/146.0
<b>Approx Initial Lumens</b>	50000
<b>Approx Mean Lumens</b>	45000
<b>CT deg K</b>	2100
<b>CRI</b>	21
<b>Rated Life</b>	24,000
<b>Common Code</b>	C400S51
<b>ANSI Ballast</b>	S51
<b>Fixt Rqmt</b>	Open
<b>Burning Position</b>	Universal
<b>Coating</b>	Clear

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975  
Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335



<b>Description</b>	400W HPS ED-18 Mogul Base
<b>Ordering Code</b>	15322
<b>UNSPSC Code</b>	39101617

## Specifications

<b>Voltage Rating</b>	100
<b>Watts</b>	400
<b>Base Type</b>	Mogul Screw (E39)
<b>Bulb Type</b>	ED-18
<b>MOL in/mm</b>	9.75/247.6
<b>MOD in/mm</b>	2.28/58.0
<b>LCL in/mm</b>	5.75/146.0
<b>Approx Initial Lumens</b>	50000
<b>Approx Mean Lumens</b>	45000
<b>CT deg K</b>	2100
<b>CRI</b>	21
<b>Rated Life</b>	24,000
<b>Common Code</b>	C400S51
<b>ANSI Ballast</b>	S51
<b>Fixt Rqmt</b>	Open
<b>Burning Position</b>	Universal
<b>Coating</b>	Clear

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335