



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LU70HECO 70W ED23.5 High Pressure Sodium Clear Mogul Base

Ge By Current Lamps

Catalog Number	LU70HECO
Manufacturer	Ge By Current Lamps
Description	Ge Ecolux®, 85368, 70 WTT, 1.6 Amp, 6400 LM, 1900 KV, 22 Cri, Mogul Screw (E39) Base, 24000 HR Average Life
Weight per unit	0.3500 (lbs/each)
Product Category	Hid High Pressure Sodium Lamps

Features

amperage rating	1.6
average life	24000.0
Base	Mogul Screw (E39)
lumens	6400.0
Wattage	70.0

Material, Color, and Finish

Color	Clear
color rendering index (cri)	22.0
color temperature	1900.0
Finish	Clear
Style	Open or enclosed fixtures

Descriptions

Description	70W ED23.5 HIGH PRESSURE SODIUM CLEAR MOGUL BASE
extra long description	GEL LU70/H/ECO 85368 LUCALOX
Long Description	GE Ecolux®, 85368, 70 WTT, 1.6 AMP, 6400 LM, 1900 KV, 22 CRI, Mogul Screw (E39) Base, 24000 HR Average Life
Product Type	85368 Lucalox
Special Features	7.75IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168853682
Manufacturers Part Number	LU70/H/ECO
UPC	043168853682

Taxonomies, Classifications, and Categories

Category Description	SODIUM
----------------------	--------

Packaging

Carton	1
Package	12
Weight Per each	0.35



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Universal burning position