



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



LU70MEDECO 70W E17 High Pressure Sodium Clear Med Base Lamp

Ge By Current Lamps

Catalog Number	LU70MEDECO
Manufacturer	Ge By Current Lamps
Description	Ge Lucalox®, 11339, 70 WTT, 6400 LM, 1900 KV, 22 Cri, Medium Screw (E26) Base, 24000 HR Average Life
Weight per unit	0.1700 (lbs/each)
Product Category	Hid High Pressure Sodium Lamps

Features

average life	24000
Base	E26
lumens	6400
Wattage	70

Material, Color, and Finish

Color	Clear
color rendering index (cri)	22.0
color temperature	1900.0
Finish	Clear
Style	Open or enclosed fixtures

Descriptions

Description	70W E17 HIGH PRESSURE SODIUM CLEAR MED BASE LAMP
extra long description	GEL LU70/MED/ECO 11339 LUCALOX
Long Description	GE Lucalox®, 11339, 70 WTT, 6400 LM, 1900 KV, 22 CRI, Medium Screw (E26) Base, 24000 HR Average Life
Product Type	11339 Lucalox
Special Features	5.43IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168113397
Manufacturers Part Number	LU70/MED/ECO
UPC	043168113397

Taxonomies, Classifications, and Categories

Category Description	SODIUM
----------------------	--------

Packaging

Carton	1
Package	6
Weight Per each	0.17

Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------