



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## LU70MEDECO 70W E17 High Pressure Sodium Clear Med Base Lamp

*Ge By Current Lamps*

Catalog Number	LU70MEDECO
Manufacturer	Ge By Current Lamps
Description	Ge Lucalox®, 11339, 70 WTT, 6400 LM, 1900 KV, 22 Cri, Medium Screw (E26) Base, 24000 HR Average Life
Weight per unit	0.1700 (lbs/each)
Product Category	Hid High Pressure Sodium Lamps

### Features

average life	24000
Base	E26
lumens	6400
Wattage	70

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	22.0
color temperature	1900.0
Finish	Clear
Style	Open or enclosed fixtures

### Descriptions

Description	70W E17 HIGH PRESSURE SODIUM CLEAR MED BASE LAMP
extra long description	GEL LU70/MED/ECO 11339 LUCALOX
Long Description	GE Lucalox®, 11339, 70 WTT, 6400 LM, 1900 KV, 22 CRI, Medium Screw (E26) Base, 24000 HR Average Life
Product Type	11339 Lucalox
Special Features	5.43IN Length

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168113397
Manufacturers Part Number	LU70/MED/ECO
UPC	043168113397

### Taxonomies, Classifications, and Categories

Category Description	SODIUM
----------------------	--------

### Packaging

Carton	1
Package	6
Weight Per each	0.17

### Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------