



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

IMAGE
COMING
SOON

M175MULTIKIT *Delisted* Ballast MH M175/120-277/Multi Kit *Sylvania-Ledvance*

Catalog Number	M175MULTIKIT
Manufacturer	Sylvania-Ledvance
Description	OBS47735 120/208/240/277V Multi Tap Magnetic Core and Coil Ballast For 175W Metal Halide Lamp
Weight per unit	7.8 (lbs/each)
Product Category	Magnetic Hid Ballasts

Features

amperage rating	1.8, 1.04, 0.9, 0.78
ANSI Code	M57, H39
Ballast Factor	1
Lamp Type	METALARC METAL HALIDE MAGNETIC
Minimum Starting Temperature	-22.000000000000000
Number of Lamps	1
Power Factor	>0.9
start type	OCV
total harmonic distortion	<20
Voltage Rating	120, 208, 240, 277
Wattage	175

Dimensions and Weight

Height	5.435000000000000
Length	7.100000000000000
Width	7.100000000000000

Descriptions

Description	*DELISTED* BALLAST MH M175/120-277/MULTI KIT
extra long description	SYL M175/MULTI-KIT/47735 M175MULTIK
Long Description	OBS47735 120/208/240/277V multi tap magnetic core and coil ballast for 175W metal halide lamp
Product Type	M175MULTIKIT 1/CS 1/Sku
Special Features	Multi Tap, Magnetic Core and Coil, Circuit Type Constant Wattage Autotransformer, Input Power 210 WAT, Open Circuit Voltage 305 V, Ground Ballast Core, Class P

Manufacturer Information

Brand	OSRAM
GTIN	00046135477355
Manufacturers Part Number	M175/MULTI-KIT/47735
UPC	046135477355



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description HID BALLASTS

Type Magnetic HID Ballast

Packaging

Carton 1

Weight Per each 7.8

Uses, Certifications, and Standards

standard M57