



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



M22SDLGK10G III Mom PB BLK-BZL FLSH GRN 12-30VAC/DC Eaton Corp

Catalog Number	M22SDLGK10G
Manufacturer	Eaton Corp
Description	Eaton M22 Modular Pushbutton, Complete Device, 22.5 MM, Flush, Momentary, Illuminated, Bezel: Black, Button: Green, 1NO, IP67, IP69K, Nema 4X, 13, 12-30 Vac/DC
Weight per unit	0.0680 (lbs/each)
Product Category	Push Button Complete Assemblie

Features

actuator	Button, Flush
Contact Configuration	1 NO
Voltage Rating	12-30 Vac/dc

Dimensions and Weight

Depth	1.46
Height	2.16
Size	22.5 mm
Width	1.18

Descriptions

Description	ILL MOM PB BLK-BZL FLSH GRN 12-30VAC/DC
extra long description	ETN M22S-DL-G-K10-G NEMA 4X, 13, 12
Features	This attractive, functional line of pushbuttons features a space-saving construction that enables fast assembly. The complete illuminated M22 line offers LED light units to ensure high-quality brightness and up to 100,000 hours of illumination. Because of the rugged design of these pushbuttons, most operators and contact blocks exceed five million mechanical operations.
Long Description	Eaton M22 modular pushbutton, Complete Device, 22.5 mm, Flush, Momentary, Illuminated, Bezel: Black, Button: Green, 1NO, IP67, IP69K, NEMA 4X, 13, 12-30 Vac/dc
Product Type	Nema 4X, 13, 12-30 Vac/DC
Special Features	M22 series

Manufacturer Information

Brand	Eaton
GTIN	00786685274249
Manufacturers Part Number	M22S-DL-G-K10-G
Model	Modular pushbutton
UPC	786685274249



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description MINATURE PILOT DEVICES.22MM

Packaging

Carton 1

Weight Per each 0.068

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels
and OEMs

environmental conditions IP67, IP69K, NEMA 4X, NEMA 13

standard Lloyd's Register Certified,CCC Marked,CSA Certified,CE
Marked,Bureau Veritas,GoST-R