



MILBANK[®]
ENERGY AT WORK

M400-UG-APS-LC



Catalog Number	M400-UG-APS-LC	Mounting	Surface Mount
Marketing Product Description	4 Terminal Ring Type Plain Top 1-200 Ampere Main Breaker 24 Branch Circuit	Enclosure	G90 Galvanized Steel with Powder Coat Finish
UPC	784572116238	Jaw Quantity	4 Terminal
Length (IN)	6	Bypass Type	No Bypass
Width (IN)	28	Number of Meter Positions	1 Position
Height (IN)	40	Equipment Ground	Ground Bar
Brand Name	Milbank	Hub Opening	Plain Top
Type	Ring Type Meter Socket	Line Side Wire Range	6 AWG - 350 kcmil
Application	Meter Socket With Main And Load Center	Number Branch Circuits	12
Standard	UL Listed;Type 3R	Number Of Receptacles	0
Voltage Rating	Up to 240 Volts Alternating Current		
Amperage Rating	320 Continuous Ampere		
Phase	1 Phase		
Frequency Rating	60 Hertz		
Size	6L x 28W x 40H		
Number Of Cutouts	2		
Cutout Size	Two 200 Ampere Main Breakers		
Cable Entry	Underground		
Terminal	Single Mechanical		
Insulation	Glass Polyester		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.