



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## M619427 Self-Laminating Vinyl Wrap Around Labels 1" H X 1"

*Brady Worldwide, Inc.*

Catalog Number	M619427
Manufacturer	Brady Worldwide, Inc.
Description	Self-Laminating Vinyl Wrap Around Labels 1 In H X 1 In W WT, Clear RL/250
Weight per unit	0.1550 (lbs/each)
Product Category	20230207130857

### Features

labels per package	Roll of 250 Labels
Material	Self-Laminating Vinyl
Shape	Square
Temperature Range	-94 °F - 158 °F
Wire Size	0.118 in to 0.199 in

### Material, Color, and Finish

Color	White, Clear
Finish	Matte

### Dimensions and Weight

Height	1
Size	1 in H x 1 in W
Thickness	0.004
Width	1

### Descriptions

Description	SELF-LAMINATING VINYL WRAP AROUND LABELS 1" H X 1"
extra long description	BRADY M6-19-427 Label 1 x 1 Self-la
Features	Self-laminating vinyl material is excellent for wire and cable identification. Designed with a clear protective layer to cover the printed text, B-427 material provides superb protection from abrasion, dirt, oils, solvents, water and excess handling.
Long Description	Self-Laminating Vinyl Wrap Around Labels 1 in H x 1 in W WT, Clear RL/250
Product Type	Label 1 X 1 Self-Lam Vinyl WT/CL RL/250
Special Features	Self Laminating & Wrap Around

### Manufacturer Information

Brand	Brady®
GTIN	00888434600368
Manufacturers Part Number	M6-19-427
UPC	888434600368



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... Fuses & Fuse Accessories .....

## Packaging

Carton ..... 1 .....

Weight Per each ..... 0.155 .....

## Uses, Certifications, and Standards

Application ..... Data and Telecommunications Labeling;Electrical  
Labeling;Laboratory Labeling;Wire and Cable Labeling .....

standard ..... ASTM D 1000;ASTM D 2979;ASTM G 155;UL Recognized .....