



Powering Business Worldwide

pe.eaton.com

Eaton's Meter Breaker EUSERC

MBE4040B200BTS

UPC:782114849194

Dimensions:

- **Height:** 34.38 IN
- **Length:** 5.38 IN
- **Width:** 22 IN

Weight:57 LB

Warranties:

- 10 year

Specifications:

- **Type:** All-in-ones
- **Amperage Rating:** 200A
- **Box Size:** D
- **Bus Material:** Aluminum
- **Enclosure:** NEMA 3R
- **Feed Type:** Top/bottom
- **Ground:** #6-250 kcmil
- **Interrupt Rating:** 22 kAIC
- **Main Circuit Breaker:** CSR2200
- **Mounting:** Surface
- **Number Of Circuits:** 40
- **Number Of Jaws:** Four-jaw
- **Number Of Sockets:** 1
- **Phase:** Single-phase
- **Security:** Ring
- **Used With:** Type BR breakers
- **Voltage Rating:** 120/240V

Supporting documents:

- [Dimensional Drawing - METER BREAKER PHOENIX STYLE](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Technical Data Residential Meter Breakers:](#)



Type CH and BR Residential

Certifications:

- UL Listed

Product compliance:

- EUSERC Approved

© 2016 Eaton. All rights reserved.