



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MC122BLWH 12/2 WG MC BL/WH/GN Alu Armor 250' *Southwire Company*

Catalog Number	MC122BLWH
Manufacturer	Southwire Company
Description	Aluminum Armored Conductor, Solid, #12 Awg Conductor Size, PVC Jacket Material, Thermoplastic Nylon Insulation Material, Copper Conductor Material, 600 V, 20 A, Blue, White and Green. 2 Conductors, 250 FT Overall Length, 0.475 In Outside Diameter, +75C (Wet) Operating Temperature, 104 LB/MFT
Weight per unit	0.1050 (lbs/ft)
Product Category	Alum Armor Copper Conductors

Features

*comes w/ bk/rd/grn covers	-
media	Yes

Material, Color, and Finish

Color	blue/white/green
Jacket Color	

Dimensions and Weight

Length	250
--------	-----

Descriptions

Description	12/2 WG MC BL/WH/GN ALU ARMOR 250'
extra long description	SWC 68948901 Armorlite Type MC
Long Description	Aluminum Armored Conductor, Solid, #12 AWG Conductor Size, PVC Jacket Material, Thermoplastic Nylon Insulation Material, Copper Conductor Material, 600 V, 20 A, Blue, White and Green. 2 Conductors, 250 ft Overall Length, 0.475 in Outside Diameter, +75C (Wet) Operating Temperature, 104 lb/mft

Manufacturer Information

GTIN	00032886347535
Manufacturers Part Number	68948901
UPC	032886347535

Taxonomies, Classifications, and Categories

Category Description	BX & MC
Type	MC

Packaging

Carton	250
Weight Per foot	0.105