



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MC123BR0RGYGN 12/3 WG MC Sol BR/or/Gy/GN Steel Armor 250' *Southwire Company*

Catalog Number	MC123BR0RGYGN
Manufacturer	Southwire Company
Description	MC Tuff Type MC Cable, Traditional Lightweight, With Ground and Neutral, 3 Conductors, 12 Awg Conductor and Ground, Solid Copper, Outside Diameter: 0.53 In, 600 V, 90 Deg C (Dry), THHN Insulation, Polypropylene Tape Shield, Galvanized Interlocking Steel Strip (Blue Striped) Armor, Color: 408Y/277V: Brown, Orange, Gray, Green, 250 FT Coil, Weight: 186 LB/1000 FT, UI 83, 1479, 1569, 1581, 2556 File Number E80042, UI File Number R-14141, Nec 230.43, 300.22(C), 392, 396, 330, 501, 502, 503, 530, 504, 505, 518,
Weight per unit	0.1400 (lbs/ft)
Product Category	Teck

Features

Conductor Size	12 AWG Conductor And Ground
Number of Conductors	3
outside diameter	0.53
Voltage Rating	600

Material, Color, and Finish

Color	408Y/277Y: Brown, Orange, Gray, Green
Conductor Material	Solid Copper
Insulation Material	THHN

Dimensions and Weight

Length	250 FT Coil
--------	-------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	12/3 WG MC SOL BR/OR/GY/GN STEEL ARMOR 250'
extra long description	KT 1705B42T01 12-3 MC TUFF BN OE GY
Long Description	MC TUFF Type MC Cable, Traditional Lightweight, With Ground And Neutral, 3 Conductors, 12 AWG Conductor And Ground, Solid Copper, Outside Diameter: 0.53 IN, 600 V, 90 DEG C (Dry), THHN Insulation, Polypropylene Tape Shield, Galvanized Interlocking Steel Strip (Blue Striped) Armor, Color: 408Y/277V: Brown, Orange, Gray, Green, 250 FT Coil, Weight: 186 LB/1000 FT, UL 83, 1479, 1569, 1581, 2556 File Number E80042, UL File Number R-14141, NEC 230.43, 300.22(C), 392, 396, 330, 501, 502, 503, 530, 504, 505, 518,
Product Type	12-3 MC Tuff BN Oe Gy GN 250' Coil
Special Features	Cable tray rated, install per NEC; May be surfaced mounted and embedded in plaster; Environmental air-handling space installation per NEC 300.22; UL Classified 1, 2, and 3 hour through (Fire) penetration product, R-14141; Made in USA of US and/or imported materials; ColorSpec ID system

Manufacturer Information

Brand	Flexible Conduit
GTIN	00077680195593
Manufacturers Part Number	1705B42T01
UPC	077680195593

Taxonomies, Classifications, and Categories

Category Description	BX & MC
Type	Traditional Lightweight Type MC Cable With Ground And Neutral

Availability

Status	Inactive
--------	----------

Packaging

Carton	250
Weight	186
Weight Per foot	0.14

Uses, Certifications, and Standards

standard	UL 83, 1479, 1569, 1581, 2556 File Number E80042, UL File Number R-14141, NEC 230.43, 300.22(C), 392, 396, 330, 501, 502, 503, 530, 504, 505, 518, 520, 530, 645, Federal Specification A-A-59544 (Formerly J-C-30B), Meets OSHA And HUD Requirements, ISO 9001 Certified
Temperature Rating	90 Deg C (Dry)