



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MC123BRYLGY250 12/3 WG MC Sol BR/YI/Gy Alu Armor 250' *Southwire Company*

Catalog Number	MC123BRYLGY250
Manufacturer	Southwire Company
Description	Aluminum Armored Cable, MC Type; 250 FT; 0.539 Inch Outer Diameter; Soft Drawn Copper Conductor Material; UI 83/1569/1685 Approval; 277/480/600 V Voltage Rating; 90 Deg C Temperature Rating; 3 Conductor(S); THHN/THWN Insulation Material; 12 Awg Conductor Size
Weight per unit	0.1290 (lbs/ft)
Product Category	Wire

Features

Conductor Size	12
media	Yes
Number of Conductors	3
outside diameter	0.50478
Voltage Rating	600V

Material, Color, and Finish

Conductor Material	CU
--------------------	----

Dimensions and Weight

Length	250
--------	-----

Descriptions

Description	12/3 WG MC SOL BR/YL/GY ALU ARMOR 250'
extra long description	SWC 61052301 Armorlite Type MC
Long Description	ALUMINUM ARMORED CABLE, MC TYPE; 250 FT; 0.539 INCH OUTER DIAMETER; SOFT DRAWN COPPER CONDUCTOR MATERIAL; UL 83/1569/1685 APPROVAL; 277/480/600 V VOLTAGE RATING; 90 DEG C TEMPERATURE RATING; 3 CONDUCTOR(S); THHN/THWN INSULATION MATERIAL; 12 AWG CONDUCTOR SIZE
Product Type	Armorlite Type MC

Manufacturer Information

Brand	Flexible Conduit
GTIN	00032886026720
Manufacturers Part Number	61052301
UPC	032886026720

Taxonomies, Classifications, and Categories

Category Description	BX & MC
Type	MC



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight	32.215
Weight Per foot	0.129