



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MC70T6UG12830 70W T6 G12 3K Metal Halide Tubular Lamp

Sylvania-Ledvance

Catalog Number	MC70T6UG12830
Manufacturer	Sylvania-Ledvance
Description	Metalarc Powerball 70W Ceramic Metal Halide Tubular T6, Clear, Universal Operation, G12 Base, 3000K CCT, 87 Cri, Pulse Start, Enclosed Rated, 15000 Hour Rated Life
Weight per unit	0.1060 (lbs/each)
Product Category	Hid Ceramic Metal Halide Lamps

Features

average life	15000
Base	G12
Fixture Type	Enclosed
lumens	7,400
Shape	T6
start type	Pulse
Voltage Rating	230
Wattage	74

Material, Color, and Finish

color rendering index (cri)	90
color temperature	3000
Finish	Clear

Dimensions and Weight

Size	5.59
------	------

Descriptions

Description	70W T6 G12 3K METAL HALIDE TUBULAR LAMP
extra long description	SYL MC70T6UG12830/64969 MC70T6UG128
Long Description	METALARC POWERBALL 70W ceramic metal halide tubular T6, clear, universal operation, G12 base, 3000K CCT, 87 CRI, pulse start, enclosed rated, 15000 hour rated life
Product Type	MC70T6UG12830 12/CS 1/Sku
Special Features	T6, clear, universal operation, G12 base, 3000K CCT, 87 CRI, pulse start, enclosed rated, 15,000 hour rated life

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135649691
Manufacturers Part Number	MC70T6/U/G12/830/64969
UPC	046135649691

Taxonomies, Classifications, and Categories

Type	High Intensity Discharge (HID)
------	--------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.106

Uses, Certifications, and Standards

Application	SPECIALTY
standard	C139/E