



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MDL10 10A 32V TD Glass Fuse

Bussmann Fuses

Catalog Number	MDL10
Manufacturer	Bussmann Fuses
Description	10A 32V 3AG - 1/4" X 1-1/4" Glass, Time Delay Fuse
Weight per unit	0.0070 (lbs/each)
Product Category	Tools & Testers

Features

amperage rating	10 Amp
connection	Ferrule End X Ferrule End
Response Time	60 Min Maximum at 135%, 120 S Maximum at 200%
type of indicators	Non-Indicating
Voltage Rating	32 VAC

Dimensions and Weight

Size	1/4 In Diameter X 1-1/4 In Length
------	-----------------------------------

Descriptions

Description	10A 32V TD GLASS FUSE
extra long description	EFSE MDL-10 BUSS SMALL DIMENSION FU
Long Description	10A 32V 3AG - 1/4" x 1-1/4" Glass, Time Delay Fuse
Product Type	Buss Small Dimension Fuse
Special Features	Interrupt Rating 1000 Amp at 32 Vac, Material Glass Tube, Nickel Plated Brass Endcap

Manufacturer Information

Brand	Cooper Bussmann North America
GTIN	00051712724579
Manufacturers Part Number	MDL-10
UPC	051712724579

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Electronic, Time Delay

Availability

Status	Inactive
--------	----------

Packaging

Carton	5
Weight Per each	0.007

Uses, Certifications, and Standards

Application	Electronic Circuits
standard	UL 248-14, CSA, CE