



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MDL610 6/10A Glass Fuse

Bussmann Fuses

Catalog Number	MDL610
Manufacturer	Bussmann Fuses
Description	6/10A 250V 3AG - 1/4" X 1-1/4" Glass, Time Delay Fuse
Weight per unit	0.0100 (lbs/each)
Product Category	Tools & Testers

Features

amperage rating	6/10 Amp
connection	Ferrule End X Ferrule End
Response Time	60 Min Maximum at 135%, 5 S Minimum at 200%, 120 S Maximum at 200%
type of indicators	Non-Indicating
Voltage Rating	250 VAC

Dimensions and Weight

Size	1/4 In Diameter X 1-1/4 In Length
------	-----------------------------------

Descriptions

Description	6/10A GLASS FUSE
extra long description	EFSE MDL-6/10 BUSS SMALL DIMENSION
Long Description	6/10A 250V 3AG - 1/4" x 1-1/4" Glass, Time Delay Fuse
Product Type	Buss Small Dimension Fuse Slow Blow
Special Features	Interrupt Rating 35 Amp at 250 Vac, 10000 Amp at 125 Vac, Material Glass Tube, Nickel Plated Brass Endcap

Manufacturer Information

Brand	Cooper Bussmann North America
GTIN	00051712724395
Manufacturers Part Number	MDL-6/10
UPC	051712724395

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Electronic, Time Delay

Packaging

Carton	1
Package	5
Weight Per each	0.01

Uses, Certifications, and Standards

Application	Electronic Circuits
standard	UL 248-14, CSA, CE