



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MEQ8 8A 500V Fiber Tube Time Delay Midget Fuse

Edison Fuses

Catalog Number	MEQ8
Manufacturer	Edison Fuses
Description	Eaton Edison Meq Fuse, Supplemental Protection Of Transformers, Solenoids, and Other High Inrush Circuits., 8 A, Non-Indicating, 10 Kaic At 500 Vac, Fiber Tube, Standard, 500 V
Weight per unit	0.0300 (lbs/each)
Product Category	Dual Element

Features

amperage rating	8 Amp
amps	8
class	Supplemental
connection	Ferrule End X Ferrule End
dimensions	1.0000 IN X 0.4060 IN X 0.4060 IN
Fuse Type	Midget Time Delay Fuses
interrupt rating	10 kA (RMS Symmetrical)
Material	Fiber Tube
type of indicators	Non-Indicating
Voltage	500V
Voltage Rating	500 VAC

Dimensions and Weight

Size	13/32 In Diameter X 1-1/2 In Length
------	-------------------------------------

Descriptions

Description	8A 500V FIBER TUBE TIME DELAY MIDGET FUSE
extra long description	MOR T626-MEQ8 Midget Time Delay Fus
Features	Edison offers a broad selection of Supplemental and Midget Fuses in both Time-delay and Fast-acting designs with voltages as high as 600Vac and 600Vdc
Long Description	Eaton Edison MEQ fuse, Supplemental protection of transformers, Solenoids, and other high inrush circuits., 8 A, Non-indicating, 10 kAIC at 500 Vac, Fiber tube, Standard, 500 V
Product Type	Midget Time Delay Fuses 500V 8a

Manufacturer Information

Brand	Eaton
GTIN	00782634786085
Manufacturers Part Number	MEQ8
UPC	782634786085



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	MIDGET FUSES
Type	FUSE

Packaging

Carton	1
Package	10
Weight Per each	0.03

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems
standard	RoHS Compliant,Not Applicable