



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MLT4HLP Steel-Ty* Stra *Panduit Corporation*

Catalog Number	MLT4HLP
Manufacturer	Panduit Corporation
Description	The MLT4H-LP Self-Locking Cable Tie Speeds Up Installation With A Unique Self-Locking Head Design That Locks Into Place At Any Part Of The Tie Body. The Smooth Surfaces and Rounded Edges Assure Cable Protection and Worker Safety While Providing A Strong, Durable Method Of Cabling Bundle. The MLT4H-LP Cable Tie Can Be Used In A Wide Range Of Indoor, Outdoor, and Underground Applications. Color Stainless Steel.
Weight per unit	0.8014 (lbs/each)
Product Category	Cable Ties & Wraps

Features

media	Yes
Tensile Strength	450

Dimensions and Weight

Length	14.3
--------	------

Descriptions

Description	STEEL-TY* STRA
extra long description	PAN MLT4H-LP Pan-Steel® MLT4H-LP Ca
Long Description	The MLT4H-LP self-locking cable tie speeds up installation with a unique self-locking head design that locks into place at any part of the tie body. The smooth surfaces and rounded edges assure cable protection and worker safety while providing a strong, durable method of cabling bundle. The MLT4H-LP cable tie can be used in a wide range of indoor, outdoor, and underground applications. Color Stainless Steel.
Product Type	Pan-Steel® MLT4H-LP Cable Tie, SS 304, Heavy, 4" Dia., PK50
Special Features	Indoor/Outdoor

Manufacturer Information

Brand	Panduit®
GTIN	00074983543878
Manufacturers Part Number	MLT4H-LP
UPC	074983543878

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	50
Package	250
Weight Per each	0.8014

Uses, Certifications, and Standards

Application	General
standard	UL E56854,CE,ABS,GL,SAE,BV,LR,DNV,USCG