



TWO GANG WIU COVERS

**Two Gang - While In use Covers
2-Gang 55-in-1**

C05



Catalog #: MM2410C

APPLICATIONS

Designed for use whenever weatherproof protection is required while an outlet is in use.
N/A

PRODUCT FEATURES

High-impact polycarbonate construction provides maximum durability
Patented Quick-Fit™ keyhole mounting system allows installation in under a minute.
Includes attached gasket and mounting hardware
Pre-configured for GFCI with patented Knockout technology for alternate devices
Lockable tab

UL LISTED

File E116141

NEMA

3R Rated

NEC

2014 Compliant (article 406.9A)

US PATENTS

8,314,335

GENERAL PRODUCT INFORMATION

Color: Clear
Country of Origin: USA

CONFIGURATION

Gangs: 2

PRODUCT MEASUREMENTS

Depth: 2-3/4 in.
Wt. Ea. (Lbs.): 0.700

PACKAGING

Package Type: Shrink
Std. Pkg.: 6
Product UPC-A Labeled: Yes
Weight (Lbs. Per/C): 70.00
Ship Carton Length (in.): 19.75
Ship Carton Width (in.): 5.88
Ship Carton Height (in.): 6.38
Ctn Weight (Lbs.): 4.20
Pallet Qty: 504.00
UPC Number: 092326104067
I2of5: 60092326104069