



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MP400BUONLY 400 MH Lamp, Open Rated

Sylvania-Ledvance

Catalog Number	MP400BUONLY
Manufacturer	Sylvania-Ledvance
Description	400W Metalarc Pro Tech Quartz Metal Halide Lamp, EX39 Base, BT37 Bulb, Open Fixture Rated, Base Up Only, Clear, 3600K
Weight per unit	1.2 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

average life	20000
Base	EX39 Exclusionary Mogul
lumens	40000
Shape	BT37
Voltage Rating	135
Wattage	400

Material, Color, and Finish

color rendering index (cri)	65
color temperature	3600
Finish	COATED

Dimensions and Weight

Size	11.5
------	------

Descriptions

Description	400 MH LAMP, OPEN RATED
extra long description	SYL MP400/BU-ONLY/64705 MP400BUONLY
Long Description	400W METALARC PRO TECH quartz metal halide lamp, EX39 base, BT37 bulb, open fixture rated, base up only, clear, 3600K
Product Type	MP400BUONLY 6/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135647055
Manufacturers Part Number	MP400/BU-ONLY/64705
UPC	046135647055

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
Type	High Intensity Discharge (HID)

Packaging

Carton	1
Package	6
Weight Per each	1.18



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

standard

M59/O
