



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MP50UMED 50W P/S MH E17 Clear Bulb Med Screw Base 3000K La *Sylvania-Ledvance*

Catalog Number	MP50UMED
Manufacturer	Sylvania-Ledvance
Description	50W Metalarc Pro Tech Pulse Start Quartz Metal Halide Lamp, Reduced Color Shift, Med Base, E17 Bulb, Open Fixture Rated, Universal Burn, Clear, 3000K
Weight per unit	0.2900 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	E26 Medium
lumens	3450
Shape	E17
Voltage Rating	85

Material, Color, and Finish

color rendering index (cri)	70
-----------------------------	----

Dimensions and Weight

Size	5.43
------	------

Descriptions

Description	50W P/S MH E17 CLEAR BULB MED SCREW BASE 3000K LA
extra long description	SYL MP50/U/MED/64587 MP50UMED 20/CS
Long Description	50W METALARC PRO TECH PULSE START quartz metal halide lamp, reduced color shift, MED base, E17 bulb, open fixture rated, universal burn, clear, 3000K

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135645877
Manufacturers Part Number	MP50/U/MED/64587
UPC	046135645877

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
Type	High Intensity Discharge (HID)

Packaging

Carton	1
Package	20
Weight Per each	0.29

Uses, Certifications, and Standards

standard	M110/O
----------	--------