



MPAP-200-MB-78

Catalog Number	MPAP-200-MB-78	Mounting	Pedestal
Marketing Product Description	4 Terminal Ring Type Plain Top 1-200 Ampere Main Breaker Single Pedestal Direct Bury Parallel Wired	Enclosure	G90 Galvanized Steel with Powder Coat Finish
UPC	784572166400	Jaw Quantity	4 Terminal
Length (IN)	4	Bypass Type	No Bypass
Width (IN)	8.156	Number of Meter Positions	1 Position
Height (IN)	78	Equipment Ground	Ground Bar
Brand Name	Milbank	Hub Opening	Plain Top
Type	Ring Type Meter Socket	Line Side Wire Range	6 AWG - 350 kcmil
Application	Mobile Home Power	Number Branch Circuits	4
Standard	UL Listed;Type 3R	Number Of Receptacles	0
Voltage Rating	Up to 240 Volts Alternating Current		
Amperage Rating	200 Continuous Ampere		
Phase	1 Phase		
Frequency Rating	60 Hertz		
Size	4L x 8.156W x 78H		
Number Of Cutouts	1		
Cutout Size	One 200 Ampere Main Breaker		
Cable Entry	Underground		
Terminal	Double Mechanical		
Insulation	Fiberglass with Resin		

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.