



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MPR400VBUH00 *Discontinued* 400W MH Lamp, Open Rated

Ge By Current Lamps

Catalog Number	MPR400VBUH00
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 3400 K, 40000 LM Brightness (Lumens), 400 W, Clear, Hard Glass Material, 20000 H Average Life, Mogul Base, M59 Ansi Ballast Code, Non Dimmable, 4.62 In Diameter, 11.5 In Height, 63 % Mercury Content, 6.54 LB
Weight per unit	0.7400 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Mogul Screw (EX39)
lumens	40000
Wattage	400

Material, Color, and Finish

Color	Clear
color rendering index (cri)	65
Finish	Clear
Style	Open or enclosed fixtures

Descriptions

Description	*DISCONTINUED* 400W MH LAMP, OPEN RATED
extra long description	GEL MPR400/VBU/HO/O 18708 MULTIVAPO
Special Features	11.5IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168187084
UPC	043168187084

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	6
Weight Per each	0.74

Uses, Certifications, and Standards

Application	Vertical base up +/-15°
-------------	-------------------------