



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MPR400VBUXHOPA 400W or PS/MH ED37 Clear Bulb Mog Screw Base 4000K

*Ge By Current Lamps*

Catalog Number	MPR400VBUXHOPA
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4000 K, 42000 LM Brightness (Lumens), 400 W, Clear, Hard Glass Material, 20000 H Average Life, EX39 Mogul Screw Base, M135/M155 Ansi Ballast Code, Non Dimmable, 4.62 In Diameter, 11.5 In Height, 41.5 % Mercury Content, 5.3 LB
Weight per unit	0.9300 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

### Features

Base	Mogul Screw (EX39)
lumens	42000.0
Wattage	400.0

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	65.0
Finish	Clear
Style	Open or enclosed fixtures

### Descriptions

Description	400W OR PS/MH ED37 CLEAR BULB MOG SCREW BASE 4000K
extra long description	GEL MPR400/VBU/XHOPA 46273 MULTIVAP
Special Features	11.5IN Length

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168462730
UPC	043168462730

### Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

### Packaging

Carton	1
Package	6
Weight Per each	0.93