



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MSCL0P153MIV Maestro 150W Led Occupancy Multi Ivory

*Lutron*

|                  |   |
|------------------|---|
| Catalog Number   | MSCL0P153MIV  |
| Manufacturer     | Lutron  |
| Description      | Maestro Occupancy Led+ Passive Infrared Occupancy/Vacancy Sensor That Automatically Controls The Lights In An Area In Ivory |
| Weight per unit  | 0.4000 (lbs/each)   |
| Product Category | Lighting Dimmers  |

### Features

|                |   |
|----------------|---|
| body           | Plastic   |
| load           | 600 W incandescent/halogen/140 W CFL/LED                                    |
| media          | Yes   |
| sensing range  | 900 ft2 (82 m2) major motion coverage/400 ft2 (36 m2) minor motion coverage |
| supply voltage | 120   |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Color  | Ivory |
| Finish | Gloss |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | MAESTRO 150W LED OCCUPANCY MULTI IVORY  |
| extra long description | LUT MSCL-OP153M-IV MAESTRO LED+ PIR   |
| Features               | The Lutron Maestro LED+ Motion Sensor Dimmer Switch works just like a Lutron Maestro dimmer, with the addition of Lutron's advanced motion sensing technology to automatically and gradually turn the lights on and off. The LED+ Motion Sensor Dimmer Switch is rated for 150W dimmable LED or 600W Incandescent/Halogen bulbs. Install in a single pole, 3-way with existing switch, or with Maestro companion dimmers (MA-R/MSC-AD) to dim from up to 9 locations. Use the raise/lower buttons to adjust the brightness for  |
| Long Description       | Maestro occupancy LED+ passive infrared occupancy/vacancy sensor that automatically controls the lights in an area in ivory   |
| Product Type           | Maestro Led+ Pir Occ Sensor Box Ivory   |
| Special Features       | Passive infrared sensors that automatically control the lights in an area. These sensors detect heat from occupants moving within an area to determine when the space is occupied. Combines a Maestro LED+ fine motion detection. 180 degree sensor field-of-view. Up to 30 ft x 30 ft (9 m x 9 m) [900 ft <sup>2</sup> (81 m <sup>2</sup> )] major motion coverage and 20 ft x 20 ft (6 m x 6 m) [400 ft <sup>2</sup> (36 m <sup>2</sup> )] minor motion coverage. Can be set to auto-on/auto-off or manual-on/auto-off. Adjustable timeout (1, 3, 5, 15, or 30 minutes) and h |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Lutron         |
| GTIN                      | 00784276054690 |
| Manufacturers Part Number | MSCL0P153MIV   |
| UPC                       | 784276054690   |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
| Type                 | Occupancy sensor dimmer, multi-location/3-way/single-pole    |

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Package         | 24  |
| Weight Per each | 0.4 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | Lighting Control                                    |
| Enclosure                | Plastic   |
| environmental conditions | 0 to 90% humidity, non-condensing. Indoor use only. |
| Mounting                 | WALLBOX   |
| Operating Temperature    | 32 to 104   |
| standard                 | UL, cUL, Title 20/24 certified                      |