



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MVR1000U **\*\*Delisted\*** 1000W BT56 Metal Halide Clear Mog Base

*Ge By Current Lamps*

|                  |   |
|------------------|---|
| Catalog Number   | MVR1000U  |
| Manufacturer     | Ge By Current Lamps   |
| Description      | Metal Halide Lamp, 65, 4000 K, 100280 LM (Horizontal);108000 LM (Vertical) Brightness (Lumens), 1000 W, Clear, Hard Glass Material, 11000 H (Horizontal);15000 H (Vertical) Average Life, Mogul Base, M47 Ansi Ballast Code, Non Dimmable, 7 In Diameter, 15.37 In Height, 150 % Mercury Content, 8.01 LB |
| Weight per unit  | 1.2 (lbs/each)  |
| Product Category | Hid Quartz Metal Halide Lamps   |

### Features

|      |                   |
|------|-------------------|
| Base | Mogul Screw (E39) |
|------|-------------------|

### Material, Color, and Finish

|                             |  |
|-----------------------------|--|
| Color                       | Clear                                      |
| color rendering index (cri) | 65   |
| Style                       | Open Fixture-Restricted Position (S-Rated) |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | <b>**DELISTED*</b> 1000W BT56 METAL HALIDE CLEAR MOG BASE |
| extra long description | GEL MVR1000/U 41826 MULTIVAPOR                            |
| Special Features       | 15.37IN Length  |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | GE Current     |
| GTIN  | 00043168418263 |
| UPC   | 043168418263   |

### Taxonomies, Classifications, and Categories

|                      |              |
|----------------------|--------------|
| Category Description | METAL HALIDE |
|----------------------|--------------|

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 6    |
| Weight Per each | 1.23 |

### Uses, Certifications, and Standards

|             |                            |
|-------------|----------------------------|
| Application | Universal burning position |
|-------------|----------------------------|