



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MVR1000UBT37 1000W BT37 Metal Halide Reduced Glass Clear Mogul

Ge By Current Lamps

Catalog Number	MVR1000UBT37
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 3700 K, 105000 LM (Horizontal);115000 LM (Vertical) Brightness (Lumens), 1000 W, Clear, Hard Glass Material, 9000 H (Horizontal);12000 H (Vertical) Average Life, Mogul Base, M47 Ansi Ballast Code, Non Dimmable, 4.625 In Diameter, 11.5 In Height, 150 % Mercury Content, 4.45 LB
Weight per unit	0.7400 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Mogul Screw (E39)
------	-------------------

Material, Color, and Finish

Color	Clear
color rendering index (cri)	65
Finish	Clear
Style	Enclosed fixtures only

Descriptions

Description	1000W BT37 METAL HALIDE REDUCED GLASS CLEAR MOGUL
extra long description	GEL MVR1000/U/BT37 18205 MULTIVAPOR
Special Features	11.5IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168182058
UPC	043168182058

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	6
Weight Per each	0.74

Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------