



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



MVR100UMED 100W BD17 Metal Halide Clear Medium Base Lamp

Ge By Current Lamps

Catalog Number	MVR100UMED
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 70, 4000 K, 9500 LM Brightness (Lumens), 100 W, Clear, Hard Glass Material, 15000 H Average Life, Medium Base, M90 Ansi Ballast Code, Non Dimmable, 2.125 In Diameter, 5.43 In Height, 8.5 % Mercury Content, 2.0 LB
Weight per unit	0.3300 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

Features

Base	Medium Screw (E26)
lumens	9500
Voltage Rating	100
Wattage	100

Material, Color, and Finish

Color	Clear
color rendering index (cri)	70
Finish	Clear
Style	Enclosed fixtures only

Descriptions

Description	100W BD17 METAL HALIDE CLEAR MEDIUM BASE LAMP
extra long description	GEL MVR100/U/MED 12652 MULTIVAPOR
Special Features	5.43IN Length

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168126526
UPC	043168126526

Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

Packaging

Carton	1
Package	6
Weight Per each	0.33

Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------