



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MVR150UMED 150W BD17 Metal Halide Clear Medium Base Lamp

*Ge By Current Lamps*

Catalog Number	MVR150UMED
Manufacturer	Ge By Current Lamps
Description	Metal Halide Lamp, 65, 4300 K, 14000 LM Brightness (Lumens), 150 W, Clear, Hard Glass Material, 15000 H Average Life, Medium Base, M102 Ansi Ballast Code, Non Dimmable, 2.125 In Diameter, 5.43 In Height, 10.8 % Mercury Content, 1.78 LB
Weight per unit	0.3000 (lbs/each)
Product Category	Hid Quartz Metal Halide Lamps

### Features

Base	Medium Screw (E26)
lumens	14000
Wattage	150

### Material, Color, and Finish

Color	Clear
color rendering index (cri)	65
Style	Enclosed fixtures only

### Descriptions

Description	150W BD17 METAL HALIDE CLEAR MEDIUM BASE LAMP
extra long description	GEL MVR150/U/MED 12598 MULTIVAPOR
Special Features	5.43IN Length

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168125987
UPC	043168125987

### Taxonomies, Classifications, and Categories

Category Description	METAL HALIDE
----------------------	--------------

### Packaging

Carton	1
Package	6
Weight Per each	0.3

### Uses, Certifications, and Standards

Application	Universal burning position
-------------	----------------------------