



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## MVR150UMED 150W BD17 Metal Halide Clear Medium Base Lamp

*Ge By Current Lamps*

|                  |   |
|------------------|---|
| Catalog Number   | MVR150UMED  |
| Manufacturer     | Ge By Current Lamps   |
| Description      | Metal Halide Lamp, 65, 4300 K, 14000 LM Brightness (Lumens), 150 W, Clear, Hard Glass Material, 15000 H Average Life, Medium Base, M102 Ansi Ballast Code, Non Dimmable, 2.125 In Diameter, 5.43 In Height, 10.8 % Mercury Content, 1.78 LB |
| Weight per unit  | 0.3000 (lbs/each)   |
| Product Category | Hid Quartz Metal Halide Lamps   |

### Features

|         |                    |
|---------|--------------------|
| Base    | Medium Screw (E26) |
| lumens  | 14000.0            |
| Wattage | 150.0              |

### Material, Color, and Finish

|                             |                        |
|-----------------------------|------------------------|
| Color                       | Clear                  |
| color rendering index (cri) | 65.0                   |
| Style                       | Enclosed fixtures only |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | 150W BD17 METAL HALIDE CLEAR MEDIUM BASE LAMP |
| extra long description | GEL MVR150/U/MED 12598 MULTIVAPOR             |
| Special Features       | 5.43IN Length                                 |

### Manufacturer Information

|       |                      |
|-------|----------------------|
| Brand | Ge Traditional Lamps |
| GTIN  | 00043168125987       |
| UPC   | 043168125987         |

### Taxonomies, Classifications, and Categories

|                      |              |
|----------------------|--------------|
| Category Description | METAL HALIDE |
|----------------------|--------------|

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Package         | 6   |
| Weight Per each | 0.3 |

### Uses, Certifications, and Standards

|             |                            |
|-------------|----------------------------|
| Application | Universal burning position |
|-------------|----------------------------|